

# Horizontal Rail, Front, Type R-KD, Rugged, Short Lip, 20 HP



Combinations of horizontal rails and side panels

\* "-" = can be combined, "+" = combination not recommended

|                            | Light rail | Standard rail | Rugged rail | Rugged rail with short lip |
|----------------------------|------------|---------------|-------------|----------------------------|
| Light rail                 | -          | +             | +           | +                          |
| Standard rail              | +          | +             | +           | +                          |
| Rugged rail                | +          | +             | -           | -                          |
| Rugged rail with short lip | +          | +             | -           | -                          |

Light rail: 1. Standard rail: 2. Rugged rail: 3. Rugged rail with short lip: 4.

## CATALOG NUMBER

**34566-220**

The rugged horizontal rail type can handle shock and vibration up to 25 g.

## FEATURES

Type R-KD "rugged" horizontal rail with 3-hole fixing for increased robustness

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings



## PRODUCT ATTRIBUTES

Rack Width: 20HP

Package Quantity: 1

Finish: Anodized

Material: Aluminum

Product Family: EuropacPRO

Product Type: Horizontal Rail

Type: Rugged, KD

Works With: Subracks

Net Weight: 0.068kg

\*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

## ADDITIONAL PRODUCT DETAILS

Without M4 thread to front, without printing and without notch for 19" bracket.

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**