

PMC Mezzanine Front Panel, Untreated, With EMC Shielding



Mezzanine front panel is fitted into PMC front panel cut-outs. Available in different treatments. For O-ring EMC gasket.

FEATURES

Mezzanine front panel is fitted into PMC front panel cut-outs

EMC shielding with conductive O-ring

Product Type: Front Panel
Type: Front Panel without Handle
EMC Shielding: Yes



SPECIFICATIONS

Table 1/2

Catalog Number	Package Quantity	Accessory Type	Mounting	Gasket Type	Front Finish	Rear Finish
20835-598	1	Front panel	Screw-on Front	O-Ring EMC	Anodized	Conductive
20835-922	1		Screw-on Front		Chrome Plated	Chrome Plated
20835-890	1		Screw-on Front			
20835-923	1		Screw-on Front		Chrome Plated	Chrome Plated
20835-889	1	Front panel	Screw-on Front	O-Ring EMC	Anodized	Conductive
20835-893	10		Screw-on Front		Chrome Plated	Chrome Plated
20835-928	10		Screw-on Front		Anodized	Conductive
20835-924	10		Screw-on Front		Chrome Plated	Chrome Plated

Table 2/2

Catalog Number	Treated Edges	Complies With	Finish	Material
20835-598	No	PMC Mezzanine, IEEE P1386	Anodized	Aluminum
20835-922	Yes	PMC Mezzanine, IEEE P1386		Zinc
20835-890	No	PMC Mezzanine, IEEE P1386		Zinc
20835-923	Yes	PMC Mezzanine, IEEE P1386		Zinc
20835-889	No	PMC Mezzanine, IEEE P1386	Anodized	Aluminum
20835-893	Yes	PMC Mezzanine, IEEE P1386		Zinc
20835-928	No	PMC Mezzanine, IEEE P1386		Zinc
20835-924	Yes	PMC Mezzanine, IEEE P1386		Zinc

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE