

RatiopacPRO Complete Desktop Case, Shielded



The nVent SCHROFF RatiopacPRO case with EMC shielding, provides electronics protection for 19" and individual electronic assemblies. This flexible and robust case is simple to convert from desktop to a 19" rack mount case and includes four different style options. This version of the case provides a sleek design for desktop applications.

FEATURES

Desktop enclosure with pre-configured components, in accordance to IEC 60297-3-101; prepared for 19" components, e.g. plug-in units and euroboards

Shielded

Version with cover strips

Ventilation slit in base plate

Rear panel perforated

Conforms with DIN EN 62368-1

Product Type: Case
Type: Case for 19" Components
Product Family: RatiopacPRO
EMC Shielding: Yes



SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Rack Width	Package Quantity	Front Frame Construction	Cooling Option	Complies With
24572-065	6U	63HP	1	Side Trim, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11

Catalog Number	Rack Height	Rack Width	Package Quantity	Front Frame Construction	Cooling Option	Complies With
24572-054	3U	84HP	1	Side Trim, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11
24572-055	3U	84HP	1	Side Trim, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11
24572-051	3U	42HP	1	Side Trim, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11
24572-056	3U	84HP	1	Side Trim, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11
24572-064	6U	42HP	1	Side Trim, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11
24572-053	3U	63HP	1	Side Trim, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11
24572-066	6U	84HP	1	Side Trim, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11
24572-067	6U	84HP	1	Side Trim, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11
24572-052	3U	42HP	1	Side Trim, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11
24572-050	3U	28HP	1	Side Trim, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11
24572-068	6U	84HP	1	Side Trim, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11

Table 2/2

Catalog Number	Finish	Material	Protection Rating
24572-065	Passivated, Powder Coated	Aluminum	IP20
24572-054	Passivated, Powder Coated	Aluminum	IP20
24572-055	Passivated, Powder Coated	Aluminum	IP20
24572-051	Passivated, Powder Coated	Aluminum	IP20
24572-056	Passivated, Powder Coated	Aluminum	IP20
24572-064	Passivated, Powder Coated	Aluminum	IP20

Catalog Number	Finish	Material	Protection Rating
24572-053	Passivated, Powder Coated	Aluminum	IP20
24572-066	Passivated, Powder Coated	Aluminum	IP20
24572-067	Passivated, Powder Coated	Aluminum	IP20
24572-052	Passivated, Powder Coated	Aluminum	IP20
24572-050	Passivated, Powder Coated	Aluminum	IP20
24572-068	Passivated, Powder Coated	Aluminum	IP20

ADDITIONAL PRODUCT DETAILS

Modifications (special colours or sizes).

Custom solutions (cut-outs in top cover, base plate or side panels).

Assembly service from 1 piece.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE