

Varistar CP Cabeling Rack



Welded steel frame for high static load requirements.
Prepared for high cable densities and 19" integration.

FEATURES

- Preconfigured, ready to use cabinet
- Static load-carrying capacity up to 1600 kg
- Ingress protection class IP 20
- Installation of different Networking equipment possible
- Integrated vertical and horizontal cable management
- Can be easily integrated into aisle containment system

Product Type: Rack
Material: Steel
Frame Material: Steel

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Cladding Material	Frame Color	Frame Color Code	Cladding Color	Cladding Color Code
10630-027	42U	Steel	Black Grey	RAL 7021	Black Grey	RAL 7021
10630-028	42U	Steel	Black Grey	RAL 7021	Black Grey	RAL 7021

Table 2/2

Catalog Number	Package Quantity	Dynamic Load	Finish
10630-027	1	2200lbf	Powder Coated
10630-028	1	2200lbf	Powder Coated

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE