

Varistar CP Top Cover Fan



Varistar Fan Top Cover with 3 Fans, expandable to 6 fans.

FEATURES

3 axial fans fitted (maximum: 6 fans)

C14 Socket

Please, review the listed product attributes to confirm every axial fan performance

Product Type: Fan
Material: Steel

SPECIFICATIONS

Table 1/2

Catalog Number	Package Quantity	Color	Color Code	Finish	Protection Rating	Works With
21630-608	1	Black Grey	RAL 7021	Powder Coated		Varistar CP
21630-602	1	Black Grey	RAL 7021	Powder Coated	IP20	
21630-737	1	Black Grey	RAL 7021	Powder Coated	IP20	
21630-603	1	Black Grey	RAL 7021	Powder Coated		Varistar CP
21630-601	1	Black Grey	RAL 7021	Powder Coated	IP20	
21630-604	1	Black Grey	RAL 7021	Powder Coated		Varistar CP
21630-605	1	Black Grey	RAL 7021	Powder Coated		Varistar CP
21630-736	1	Black Grey	RAL 7021	Powder Coated	IP20	
21630-600	1	Black Grey	RAL 7021	Powder Coated	IP20	
21630-606	1	Black Grey	RAL 7021	Powder Coated		Varistar CP
21630-607	1	Black Grey	RAL 7021	Powder Coated		Varistar CP
21630-599	1	Black Grey	RAL 7021	Powder Coated	IP20	

Catalog Number	Package Quantity	Color	Color Code	Finish	Protection Rating	Works With
21630-612	1	Black Grey	RAL 7021	Powder Coated		Varistar CP
21630-738	1	Black Grey	RAL 7021	Powder Coated	IP20	
21630-597	1	Black Grey	RAL 7021	Powder Coated	IP20	
21630-741	1	Black Grey	RAL 7021	Powder Coated	IP20	
21630-740	1	Black Grey	RAL 7021	Powder Coated	IP20	
21630-614	1	Black Grey	RAL 7021	Powder Coated		Varistar CP
21630-613	1	Black Grey	RAL 7021	Powder Coated		Varistar CP
21630-609	1	Black Grey	RAL 7021	Powder Coated		Varistar CP

Table 2/2

Catalog Number	Package Quantity	Color	Color Code	Finish	Protection Rating	Works With
21630-611	1	Black Grey	RAL 7021	Powder Coated		Varistar CP
21630-739	1	Black Grey	RAL 7021	Powder Coated	IP20	
21630-610	1	Black Grey	RAL 7021	Powder Coated		Varistar CP
21630-598	1	Black Grey	RAL 7021	Powder Coated	IP20	

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit, power cable, Thermostat or Speed controller separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE