


# Collar Screw, Cross Recess/Slotted



Integrated load spreading, replaces separate washer.  
Improved joint consistency (less variation from washer misalignment) Better vibration resistance, especially with serrated collars

## FEATURES

For assembly of partial width front panels and plug-in units

For EuropacPRO and RatiopacPRO

Cross Recess / Slotted combines advantages of both imprints: it offers a high level of torque to achieve quick and easy installation and enhances rotational leverage. It is convenient to use while offering universal tool compatibility.

Type: Screw  
Product Type: Screw



## SPECIFICATIONS

Table 1/2

| Catalog Number | Diameter | Length | Material        | Finish        | Package Quantity | Thread Size |
|----------------|----------|--------|-----------------|---------------|------------------|-------------|
| 21102-026      | 2.5mm    | 12.3mm | Steel           | Nickel Plated | 100              | M2.5        |
| 21101-102      |          | 12.3mm | Steel           | Zinc Top Coat | 100              | M2.5        |
| 21101-906      |          | 12.3mm | Stainless Steel |               | 100              | M2.5        |
| 21101-101      |          | 12.3mm | Steel           | Nickel Plated | 100              | M2.5        |
| 21101-323      |          | 11mm   |                 |               | 100              | M2.5        |

Table 2/2

| Catalog Number | Depth  | Height | Width | Works With                         | Thread Type | Torque | Certifications |
|----------------|--------|--------|-------|------------------------------------|-------------|--------|----------------|
| 21102-026      |        |        |       | Frame Type Plug-In Unit, Cassettes |             | 0.3N·m |                |
| 21101-102      | 14.3mm | 5mm    | 5mm   | Front Panels                       | Metric      | 0.3N·m | RoHS           |
| 21101-906      |        |        |       | Front Panels                       |             | 0.3N·m | RoHS           |
| 21101-101      | 14.3mm | 5mm    | 5mm   | Front Panels                       | Metric      | 0.3N·m | RoHS           |
| 21101-323      |        |        |       | Front Panels                       |             |        |                |

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**