

PSU 19" AC/DC para MicroTCA, con gestión (PM EMMC) doble tamaño completo

NÚMERO DE CATÁLOGO

11098-547



El MTCA PSU 600 es un módulo de potencia (PM) excepcionalmente eficiente para aplicaciones MicroTCA. Esta fuente de alimentación de 600W es la más eficiente disponible en formato de tamaño completo de doble ancho. El controlador de gestión integrado de este PM lo hace ideal para su uso en sistemas de comunicaciones complejos que ejecutan las últimas generaciones de procesadores y un mayor número de módulos AMC. La PSU MTCA 600 proporciona la potencia necesaria para 12 AMC, 2 unidades de enfriamiento (CU) y 2 concentradores portadores MicroTCA (MCHS).

CARACTERÍSTICAS

Doble altura ancho de tamaño completo



ATRIBUTOS DEL PRODUCTO

Tipo de producto: Suministro de energía

Tipo: 19" Modo conmutado

Compatible con: Sistemas MicroTCA

Tensión de entrada de CA: 90 – 264V

Potencia: 600W

Número de tensiones de salida: 2

Tensión 1: 12V

Corriente 1: 6.8A

Tensión 2: 3.3V

Corriente 2: 0.18A

Ancho del rack: 6HP

Fondo: 186.65mm

Altura: 148.3mm

Peso neto: 1.315kg

Cantidad del paquete: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DETALLES ADICIONALES DEL PRODUCTO

Datos de salida para Ta = 25 ... 55 °C con enfriamiento forzado de 20 cfm.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Nuestra poderosa cartera de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE