

Sensor de contacto digital (salida) para Guardian Management Gateway

NÚMERO DE CATÁLOGO

21070-124

Sensor externo de monitoreo de entradas/salidas digitales con 2 conectores RJ45. Hasta 16 sensores pueden encadenarse a través de cables de conexión y conectarse a un puerto de gestión Guardian.

CARACTERÍSTICAS

Sensor externo para el Guardian Management Gateway

Un puerto es capaz de monitorear hasta 16 dispositivos de sensor con una longitud total de cable de 40 metros

Si se conecta un sensor nVent SCHROFF Guardian, aparece en la interfaz web con el tipo y el número de serie

Carcasa metálica

Fácil montaje

2 x conexión RJ 45

Fácil cadena de margarita con cable de conexión CAT6 (o blindaje superior)



ATRIBUTOS DEL PRODUCTO

Tipo de producto: Sensor

Tipo: Contacto digital

Compatible con: Guardian Management Gateway

Peso bruto: 0.108kg

Cantidad del paquete: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Nuestra poderosa cartera de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE