

Riel horizontal, delantero, tipo R-LD, robusto, labio largo , 42 HP

NÚMERO DE CATÁLOGO

34566-342



Combinations of horizontal rails and side panels

	Light	Standard	Heavy	Super
Light	+	+	+	+
Standard	+	+	+	+
Heavy	+	+	+	+
Super	+	+	+	+

Legend: + = can be combined, - = combination not recommended

El tipo de riel horizontal resistente puede manejar golpes y vibraciones de hasta 25 g. permite el uso de manijas IEEE.

CARACTERÍSTICAS

Rieles horizontales "robustos" tipo R-LD con fijación de 3 orificios para una mayor robustez

Para la inserción/extracción de placas CompactPCI o VME64x

Con unidades HP impresas desde 28 HP hacia arriba

Longitud 20, 28, 40, 42, 63, 84 HP o 1000 mm

Extrusión de aluminio, acabado anodizado, superficie de contacto conductora, con marcas HP



ATRIBUTOS DEL PRODUCTO

Ancho del rack: 42HP

Cantidad del paquete: 1

Acabado: Anodizado

Longitud: 218.44mm

Material: Aluminio

Familia de productos: EuropacPRO

Tipo de producto: Carril horizontal

Tipo: Robusto, LD

Compatible con: Subpistas

Peso neto: 0.13kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address,

parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Nuestra poderosa cartera de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE