

Conjuntos refrigerados por conducción térmica VITA, 3UVPX48.2-PS260HTSI-311

NÚMERO DE CATÁLOGO

3UVPX48.2-PS260HTSI-311

Solicite y administre un número de pieza para todo el ensamblaje CCA, incluyendo el marcado de piezas y el etiquetado de componentes, así como registros de tarjetas, extractores, llaves de codificación, juntas EMC y almohadillas térmicas.

CARACTERÍSTICAS

Servicios completos de diseño incluyendo análisis térmico

Rápido giro 3D impreso CCA y marcos para controles de ajuste

Plantillas CAD compatibles con estándares descargables - plantillas de 3 U y 6 U disponibles

Disponible en anodizado negro, película química, acabados de níquel electroless

ESD Embalaje disponible



ATRIBUTOS DEL PRODUCTO

Tipo de producto: Bloque conductor

Compatible con: Recintos refrigerados por conducción

Fuerza de sujeción: 272 – 318kgf

Anchura de separación: PCB + (7.0 - 7.9 mm)

Característica de diseño: Tolerancia compensadora

Rendimiento térmico: El mejor

Perfil: 6.35 x 6.26 mm

Altura del rack: 3U

Material: Aluminio

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on

SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DETALLES ADICIONALES DEL PRODUCTO

From time to time, nVent may modify its product specifications to be in conformity with applicable industry, military or other relevant standards. Unless otherwise mutually agreed in writing, cancelled or superseded military specifications may be certified to the latest or superseding specifications. Products manufactured in conformity with such specifications will be deemed fully compliant whether or not you have been notified of such modifications, even if different from the original specification or those referenced by the customer.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Nuestra poderosa cartera de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE