

Unidad de ventilador de 19", 1 U, control remoto y monitoreo, 6 ventiladores, 100-240 VAC

NÚMERO DE CATÁLOGO

10713-554

Unidad de ventilador con interfaz Modbus para la instalación en un espacio de 1 U dentro del gabinete

CARACTERÍSTICAS

Temperatura controlada de velocidad del ventilador

Interfaz Modbus para monitoreo y control remoto

Umbral de temperatura para el control del ventilador ajustable en el panel frontal

Señalización del fallo del ventilador y sobre temperatura por 2 ledes y salidas de relé libres de potencial

Fuente de alimentación integrada con entrada de amplio rango (100 V - 240 V)

Menos de 1 U (42 mm) para permitir el montaje sobre guías deslizantes o cajones

2 sensores de temperatura NTC con cables incluidos



ATRIBUTOS DEL PRODUCTO

Tipo de producto: Unidad de ventiladores

Tensión de entrada de CA: 100 – 240V

Flujo de aire: 1089m³/h

Nivel de ruido: 59.5dB(A)

Potencia: 97W

Presión estática máxima: 78Pa

Temperatura ambiente: -10 to 70°C

Vida útil, L10 a 40°C: 99558h

Cantidad del paquete: 1

Acabado: Aluminio-Zinc plateado; Anodizado

Peso bruto: 5.2kg

Material: Acero; Aluminio

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Nuestro gran portafolio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE