

MTCA.4 RTM Módulo de llenado con deflector de aire, tamaño completo doble, para RTM BP Cover Z3

NÚMERO DE CATÁLOGO

21850-129

Para cubrir ranuras AdvancedMC, MCH o PM no utilizadas en sistemas MTCA.1 y MTCA.4 o ranuras no utilizadas en un sistema MTCA.0 con barra de bloqueo. Los módulos consisten en un panel frontal con cerraduras y tornillos cautivos, junta EMC y panel lateral. Los módulos se pueden fijar a la jaula de la tarjeta con los tornillos cautivos.

CARACTERÍSTICAS

De acuerdo con las especificaciones MicroTCA.1 y MicroTCA.4

Para cubrir las ranuras no utilizadas dentro de un sistema MicroTCA.1 o MicroTCA.4

Bridas con tornillos M3 cautivos para la fijación a la jaula de tarjetas

EMC blindado



ATRIBUTOS DEL PRODUCTO

Característica de diseño: Tamaño completo

Cantidad del paquete: 1

Material: Acero inoxidable

Familia de productos: MicroTCA

Tipo de producto: Módulo de sistema

Tipo: Módulo de relleno

Peso bruto: 0.361kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on

SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Nuestro gran portafolio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE