

Kit de montaje combinado para chasis, 20:62 HP

NÚMERO DE CATÁLOGO


24562-420

El montaje combinado permite la opción de dividir un subrack o caja de 6 U alto en secciones de 2 x 3 U y 6 U. Diferentes versiones están disponibles.

CARACTERÍSTICAS

Diseñado para aceptar Euroboards (100 mm de alto) y Euroboards dobles (233,35 mm de alto)

Subdivisión de la zona de concentración de 6 U en: 2 x 3 U, 1 x 6 U



ATRIBUTOS DEL PRODUCTO

Cantidad del paquete: 1

Ancho del rack 1: 20HP

Ancho del rack 2: 62HP

Material: Aluminio; Aleación de zinc

Familia de productos: EuropacPRO

Tipo de producto: Kit de montaje

Altura del rack: 6U

Tipo: Combinados

Compatible con: Subpistas

Peso neto: 0.45kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DETALLES ADICIONALES DEL PRODUCTO

Por favor ordene por separado: Panel frontal 6 U, 2 HP para cubrir el puntal.

No se pueden utilizar los siguientes guías: Tipo "accesorio", tipo "accesorio reforzado" y tipo "para PCB 4,4".

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Nuestro gran portafolio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE