

# Diapositivas telescópicas Perfil C para armario para montaje Novastar, 800 mm

## NÚMERO DE CATÁLOGO

**24562-474**

Guías telescópicas con perfil de guía para montaje en armarios con capacidad de carga de 25 kg.

## CARACTERÍSTICAS

Para montar subracks de 84 HP de ancho en el plano de 19"

Capacidad de carga: 25 kg por par

El perfil de guía (1) se ajusta a la dimensión de fijación en el gabinete (está atornillado al perfil de 19" del gabinete); el riel adaptador (3) se ajusta a la dimensión de profundidad y fijación en el subeje (se inserta en el perfil de guía como una guía telescópica)



## ATRIBUTOS DEL PRODUCTO

Familia de productos: Novastar

Fondo: 800mm

Cantidad del paquete: 2

Acabado: Anodizado

Material: Aluminio

Tipo de producto: Diapositiva telescópica

Tipo: C Perfil

Peso neto: 0.66kg

\*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DETALLES ADICIONALES DEL PRODUCTO

Sin protección contra la extracción, sin parada en la extensión completa.

El carril de refuerzo y los carriles C han sido probados de acuerdo con las normas de la autoridad rusa de energía atómica GAN.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Nuestro gran portafolio de marcas:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE