

Panel frontal RatiopacPRO EMC, ranurado, blindado, 3 U, 42 HP, 2,5 mm, AL, Anodizado delantero, Conductor trasero

NÚMERO DE CATÁLOGO


24572-604

El panel frontal EMC se puede insertar en rieles horizontales especiales con una elevación. No se necesitan tornillos para la fijación. El diseño permite a los usuarios utilizar una lámina frontal.

CARACTERÍSTICAS

La fijación no requiere tornillos

Los rieles horizontales especiales cubren los bordes del panel frontal (superior e inferior) y evitan el arqueamiento del panel frontal



ATRIBUTOS DEL PRODUCTO

Altura del rack: 3U

Ancho del rack: 42HP

Tipo de accesorio: Panel frontal

Cantidad del paquete: 1

Acabado frontal: Anodizado

Acabado trasero: Conductor

Bordes tratados: No

Fondo: 2.5mm

Acabado: Anodizado; Pasivado

Altura: 128.4mm

Material: Aluminio

Tipo de producto: Panel frontal

Anchura: 213.2mm

Peso neto: 0.55kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DETALLES ADICIONALES DEL PRODUCTO

Para obtener una caja blindada, todos los sellos EMC deben estar instalados (panel frontal/panel trasero ? panel lateral; panel lateral ? placa de cubierta; panel frontal/panel trasero ? carril horizontal; carril horizontal ? carril horizontal).

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Nuestro gran portafolio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE