

# nVent LENTON Interlok HY15LM Grout



The nVent LENTON Interlok HY15LM grout is a proprietary, nonmetallic, high-strength, nonshrink grout developed exclusively for the nVent LENTON Interlok coupling system. The nVent LENTON Interlok HY15LM grout is produced under strict nVent quality guidelines in order to ensure product quality along with consistent and reliable performance.

## CARACTERÍSTICAS

Cures quickly, allowing early removal of bracing systems

Nonmetallic grout will not rust or stain structures

Designed to provide superior dynamic, seismic and ultimate strength performance for moment frame applications

For use in pump or gravity fill applications



## ESPECIFICACIONES

| Número de catálogo | Fuerza compresiva                | Temperatura de funcionamiento | Peso por unidad | Cantidad del paquete |
|--------------------|----------------------------------|-------------------------------|-----------------|----------------------|
| HY15LM             | 24.1 MPa @ 1 d, 110.3 MPa @ 28 d | 0 to 38 °C                    | 22.68 kg        | 1                    |

**Diseñado para cumplir:** ACI 318 tipo 1-ASTM A615 grado 60;ACI 318 tipo 1-ASTM A615 grado 75;ACI 318 tipo 1-ASTM A615 grado 80;ACI 318 tipo 1-ASTM A706 grado 60;ACI 318 tipo 1-ASTM A706 grado 80;ACI 318 tipo 2-ASTM A615 grado 60;ACI 318 tipo 2-ASTM A615 grado 75

## DETALLES ADICIONALES DEL PRODUCTO

Compressive Strength is based on room temperature tests performed at 70°F (21°C).

The shelf life of nVent LENTON Interlok Grout is 12 months from the manufacturing date printed on the bag.

nVent LENTON Interlok Grout should be stored in a cool, dry environment. It is recommended that the nVent LENTON Interlok Grout be stored indoors to maintain maximum shelf life and physical properties.

Prior to installation, please read and understand the detailed instructions and safety notices provided in the nVent LENTON Interlok Instruction Manual.

| Part Number | Article Number | Rebar Size, Metric | Rebar Size, US | Rebar Size, Canada | Number of Couplers Per Bag of LENTON INTERLOK Grout |
|-------------|----------------|--------------------|----------------|--------------------|-----------------------------------------------------|
| LK5         | 145575         | 16 mm              | #5             | 15M                | 24                                                  |
| LK6         | 145580         | 20 mm              | #6             | 20M                | 25                                                  |
| LK7         | 145585         | 22 mm              | #7             | -                  | 26                                                  |
| LK8         | 145590         | 25 mm              | #8             | 25M                | 21                                                  |
| LK9         | 145595         | 28 mm              | #9             | 30M                | 17                                                  |
| LK10        | 145600         | 32 mm              | #10            | -                  | 13.5                                                |
| LK11        | 145605         | 36 mm              | #11            | 35M                | 11.5                                                |
| LK40        | 145610         | 40 mm              | -              | -                  | 7                                                   |
| LKT14       | 145611         | 43 mm              | #14            | 45M                | 7                                                   |
| LKT50       | 145615         | 50 mm              | -              | -                  | 4                                                   |
| LKT18       | 145620         | 57 mm              | #18            | 55M                | 4.5                                                 |

## ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

### Norteamérica

+1.800.753.9221

Opción 1: Atención al cliente

Opción 2: Soporte técnico

### Europa

Países Bajos:

+31 800-0200135

Francia:

+33 800 901 793

### Europa

Alemania:

800 1890272

Otros países:

+31 13 5835404

### Asia-Pacífico

Shanghái:

+86 21 2412 1618/19

Sídney:

+61 2 9751 8500



Nuestra poderosa cartera de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE