

Rack a bordo 3 U, 36 HP

NÚMERO DE CATÁLOGO

10170-015

Adecuado para vibraciones continuas, golpes, altas temperaturas y alta humedad.

CARACTERÍSTICAS

Para aplicaciones ferroviarias móviles

Adecuado para vibraciones continuas, golpes, altas temperaturas y alta humedad

Adecuado para subpistas SNCF de 1, 2 o 3 U (NF F61-005, CF 60-002)

La parte trasera está equipada para conectores estándar; la barra transversal puede ser codificada a medida para los pines de codificación SNCF

Barra transversal con canal de cable integrado

Varios bastidores se pueden apilar o montar en filas

Producido mediante un proceso de soldadura, certificado según EN 15085 (CL2)

Soldaduras de acero inoxidable pasivadas para evitar la corrosión



ATRIBUTOS DEL PRODUCTO

Familia de productos: A bordo Rack

Altura del rack: 3U

Altura: 156.7mm

Ancho del rack: 36HP

Anchura: 252.65mm

Cantidad del paquete: 1

De conformidad con: SNCF NFF 61005; SNCF NFF 60002

Fondo: 341.8mm

Material del bastidor: Acero

Material: Acero inoxidable

Tipo de producto: Rack

Carga estática: 25kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Nuestra poderosa cartera de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE