


Carril horizontal, Trasero, Tipo R-ST, Resistente, Estándar, 1000 mm

NÚMERO DE CATÁLOGO

34566-501



Combinations of horizontal rails and side panels

		$\alpha^{H=0}$ can be combined	$\alpha^{H=0}$ combination not recommended	$\alpha^{H=0}$ not supported
Aluminum		-	+	+
Aluminum 304		+	Aluminum 304 Profile for stainless steel combination	+
Aluminum 316		+	Aluminum 316 Profile for stainless steel combination	+
Polycarbonate		+	-	-
Side panel				
	Panel 1	Panel 2	Panel 3	Panel 4

El riel horizontal, tipo robusto ST permite el montaje aislado de un backplane. El aislamiento se realiza mediante una tira de aislamiento.

CARACTERÍSTICAS

Riel horizontal "robusto" tipo R-ST con fijación de 3 orificios para una mayor robustez

Extrusión de aluminio, acabado anodizado, superficie de contacto conductora, con marcas HP

Con unidades HP impresas desde 28 HP hacia arriba



ATRIBUTOS DEL PRODUCTO

Ancho del rack: 195HP

Cantidad del paquete: 1

Acabado: Anodizado

Longitud: 1000mm

Material: Aluminio

Familia de productos: EuropacPRO

Tipo de producto: Carril horizontal

Tipo: Robusto, ST

Compatible con: Subpistas

Peso neto: 0.5kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DETALLES ADICIONALES DEL PRODUCTO

Tenga en cuenta que las entregas pueden realizarse en los SPQ indicados (SPQ, por ejemplo, 5 piezas, 10 piezas, 50 piezas, etc.). Diferentes cantidades de pedido (por ejemplo, 2 piezas) se pueden cambiar a la siguiente cantidad de entrega posible = Cantidad de paquete estándar.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Nuestra poderosa cartera de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE