

# Sisäovi, ADIS

Displays and indicators can be mounted, on a surface within the enclosure while covering other components, and preventing unauthorized access.

## FEATURES

Description: For controls, meters, lamps, etc. Hinges can be mounted to allow left or right hand opening (Machining is required). Double-bit 3 mm lock, 800 mm high doors and above have 2 locks. Usable depth between inner and external door: 35 mm, adjustable depth position with AMG accessory. Workable area: H-55, W-108. 19" version available on request.

Material: Door 1.5 mm AISI 304 stainless steel and vertical top and bottom profiles 2 mm, AISI 304 stainless steel.

Protection: IP 2XC.

Finish: 400 pre-grained stainless steel.

Pack quantity: Inner door, two vertical profiles, top and bottom profiles and mounting accessories.

**Finish:** Brushed  
**Material:** Stainless Steel 304

## SPECIFICATIONS

| Catalog Number | Height | Width | Depth | Door Size    | Latch Quantity | Product Family |
|----------------|--------|-------|-------|--------------|----------------|----------------|
| ADIS06060      | 545mm  | 492mm | 15mm  | 545 x 492mm  | 1              | Wall Mounted   |
| ADIS04030      | 400mm  | 300mm | 15mm  | 345 x 192mm  | 1              | Wall Mounted   |
| ADIS06040      | 545mm  | 292mm | 15mm  | 545 x 292mm  | 1              | Wall Mounted   |
| ADIS10080      | 945mm  | 692mm | 15mm  | 945 x 692mm  | 2              | Wall Mounted   |
| ADIS05040      | 445mm  | 292mm | 15mm  | 445 x 292mm  | 1              | Wall Mounted   |
| ADIS08060      | 745mm  | 492mm | 15mm  | 745 x 492mm  | 2              | Wall Mounted   |
| ADIS12080      | 1145mm | 692mm | 15mm  | 1145 x 692mm | 2              | Wall Mounted   |
| ADIS05050      | 445mm  | 392mm | 15mm  | 445 x 392mm  | 1              | Wall Mounted   |

## ADDITIONAL PRODUCT DETAILS

To order 19"version, please add I19 to the catalogue no, e.g. ADIS04030I19. Not suitable for AFS.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**