

Teräksinen rivikaappi, pariovellinen, MCD



The mild steel double door combinable floor standing enclosure range, MCD, is ideal for installation in confined spaces where a single door, when opened, would take up too much space in front of the enclosure. The doors' loading capacity also increases as it is divided over two doors. With a IP 55 protection degree, components inside the enclosure are well protected and makes it well suited for many different applications.

INDUSTRY STANDARDS

UL 508A Listed; Type 12; File No. E92044

cUL Listed per CSA C22.2 No.0, No.0.4, No.14, No.94; Type 12; File No. E92044

NEMA/EEMAC Type 12

CSA, File No. 1442951: Type 12

IEC 62208 IP55

CE, UK CA, UL, DNV

FEATURES

Material: Frame: 1.5 mm painted steel. Doors: 2 mm painted steel. Rear, roof and side panels: 1.5 mm painted steel. Mounting plate: 3 mm galvanized steel. Bottom plates: 1 mm galvanized steel.

Frame: Seam welded reversed open profiles with 25 mm hole pattern, according to DIN 43660. Including integrated external hole pattern.

Doors: Mounted with four hinges. Including door frame with 25 mm hole pattern. Doors cannot be reversed. Separate doors to be ordered for left hand door locking.

Rear panel: Fitted by M6 torx screws. Standard facilities for rear doors mounting. Split rear panels in 1600 mm wide enclosures. RD version comes with rear door instead of rear panel.

Side panels: Supplied as an accessory.

Roof panel: Removable.

Lock: Espagnolette 4-point locking system in the main door and 2-point locking system in the secondary door. Standard double-bit lock with 3 mm insert. Standard inserts, cylinders, lift handles and T-handles are available as accessories.

Bottom plates: Consists of three or four (D>600) pieces.

Mounting plate: Double folded and slides into position. Adjustable in depth by steps of 25 mm, with the MPD02 accessory. Supplied, attached on the outside of the enclosure packaging.

Earthing: All panels are earthed through their fittings and equipped with a separate earthing stud.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP55 | TYPE 12 | IK 10.

Mounting requirements: Standard delivery ready for combined installation. For stand-alone installation add side panels.

Delivery: Frame with fitted doors, rear panel, roof panel, bottom plates, mounting plate and door frame (not included for PER5 version). For enclosures 2200 mm height, delivery includes two CMB profiles mounted in depth. Delivery also includes earthing bolts. Delivered on a pallet which is identical to the width of the enclosure to allow baying without removal. Packing material is recyclable.

Material: Mild Steel

Color Code: RAL 7035

SPECIFICATIONS

Table 1/4

Catalog Number	Article Number	Height (H)	Width (W)	Depth (D)	Mounting Plate Included	Mounting Plate Height
MCD12125PER5	MCD12125PER5	1200mm	1200mm	500mm	No	
MCD18105PER5		1800mm	1000mm	500mm	No	
MCD20124R5		2000mm	1200mm	400mm	Yes	74.57mm
MCD20104PER5		2000mm	1000mm	400mm	No	
MCD16125PER5	MCD16125PER5	1600mm	1200mm	500mm	No	
MCD20106PER5		2000mm	1000mm	600mm	No	
MCD20106R5		2000mm	1000mm	600mm	Yes	74.57mm
MCD20126RDR5		2000mm	1200mm	600mm	Yes	
MCD18125PER5		1800mm	1200mm	500mm	No	
MCD18104R5		1800mm	1000mm	400mm	Yes	66.7mm
MCD20126PER5		2000mm	1200mm	600mm	No	
MCD20085R5		2000mm	800mm	500mm	Yes	74.57mm
MCD22106R5		2200mm	1000mm	600mm	Yes	82.44mm
MCD22106PER5		2200mm	1000mm	600mm	No	
MCD18104PER5		1800mm	1000mm	400mm	No	
MCD20108RDR5		2000mm	1000mm	800mm	Yes	
MCD20108PER5		2000mm	1000mm	800mm	No	
MCD20086R5		2000mm	800mm	600mm	Yes	
MCD20164PER5		2000mm	1600mm	400mm	No	
MCD12125R5	MCD12125R5	1200mm	1200mm	500mm	Yes	

Table 2/4

Catalog Number	Article Number	Height (H)	Width (W)	Depth (D)	Mounting Plate Included	Mounting Plate Height
MCD18164R5		1800mm	1600mm	400mm	Yes	66.7mm
MCD18126R5		1800mm	1200mm	600mm	Yes	66.7mm
MCD20088R5		2000mm	800mm	800mm	Yes	74.56mm
MCD20125PER5		2000mm	1200mm	500mm	No	
MCD20108R5		2000mm	1000mm	800mm	Yes	74.57mm

Catalog Number	Article Number	Height (H)	Width (W)	Depth (D)	Mounting Plate Included	Mounting Plate Height
MCD18124PER5		1800mm	1200mm	400mm	No	
MCD20166PER5		2000mm	1600mm	600mm	No	
MCD20165PER5		2000mm	1600mm	500mm	No	
MCD16125R5		1600mm	1200mm	500mm	Yes	
MCD20086PER5		2000mm	800mm	600mm	No	
MCD20126PERDR5		2000mm	1200mm	600mm	No	
MCD14125R5		1400mm	1200mm	500mm	Yes	
MCD20128RDR5		2000mm	1200mm	800mm	Yes	
MCD18105R5		1800mm	1000mm	500mm	Yes	66.7mm
MCD18124R5		1800mm	1200mm	400mm	Yes	66.7mm
MCD20088RDR5		2000mm	800mm	800mm	Yes	
MCD14125PER5	MCD14125PER5	1400mm	1200mm	500mm	No	
MCD20164R5		2000mm	1600mm	400mm	Yes	74.57mm
MCD20105R5		2000mm	1000mm	500mm	Yes	74.57mm
MCD18164PER5		1800mm	1600mm	400mm	No	

Table 3/4

Catalog Number	Article Number	Height (H)	Width (W)	Depth (D)	Mounting Plate Included	Mounting Plate Height
MCD20125R5		2000mm	1200mm	500mm	Yes	74.57mm
MCD22126R5		2200mm	1200mm	600mm	Yes	82.44mm
MCD18085PER5		1800mm	800mm	500mm	No	
MCD20105PER5		2000mm	1000mm	500mm	No	
MCD20166R5		2000mm	1600mm	600mm	Yes	74.57mm
MCD20124PER5		2000mm	1200mm	400mm	No	
MCD20085PER5		2000mm	800mm	500mm	No	
MCD20126R5		2000mm	1200mm	600mm	Yes	74.57mm
MCD18086R5		1800mm	800mm	600mm	Yes	
MCD20088PERDR5		2000mm	800mm	800mm	No	
MCD20108PERDR5		2000mm	1000mm	800mm	No	
MCD20165R5		2000mm	1600mm	500mm	Yes	74.57mm
MCD18086PER5		1800mm	800mm	600mm	No	
MCD18085R5		1800mm	800mm	500mm	Yes	66.7mm
MCD20128PER5		2000mm	1200mm	800mm	No	
MCD18125R5		1800mm	1200mm	500mm	Yes	66.7mm
MCD20128R5		2000mm	1200mm	800mm	Yes	74.57mm
MCD20128PERDR5		2000mm	1200mm	800mm	No	
MCD18126PER5		1800mm	1200mm	600mm	No	

Catalog Number	Article Number	Height (H)	Width (W)	Depth (D)	Mounting Plate Included	Mounting Plate Height
MCD22126PER5		2200mm	1200mm	600mm	No	


Table 4/4

Catalog Number	Article Number	Height (H)	Width (W)	Depth (D)	Mounting Plate Included	Mounting Plate Height
MCD20104R5		2000mm	1000mm	400mm	Yes	74.57mm
MCD20088PER5		2000mm	800mm	800mm	No	

ADDITIONAL PRODUCT DETAILS

SPM mild steel side panels must be ordered separately to close the cabinets (individual or assembled), in order to maintain the protection rating.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE