

# Asennuslevy, GCPZ



The steel mounting plate contributes to speeding up the assembly of the console, since it can be machined easily and equipped with components before being mounted.

## FEATURES

Description: Standard mounting plate for MPG(S) console.  
Adjustable in depth using MPGDA accessory.

Material: 2.5 mm galvanized steel.

Pack quantity: 1 plate with mounting accessories.

**Thickness:** 2.5mm  
**Material:** Galvanized Steel  
**Finish:** Plated

## SPECIFICATIONS

| Catalog Number | Height | Width  | Depth | Fits Enclosure Width | Panel Size   | Enclosure Material          |
|----------------|--------|--------|-------|----------------------|--------------|-----------------------------|
| GCPZ08         | 790mm  | 800mm  | 24mm  | 800mm                | 790 x 699mm  | Mild Steel, Stainless Steel |
| GCPZ16         | 790mm  | 1600mm | 24mm  | 1600mm               | 790 x 1499mm | Mild Steel, Stainless Steel |
| GCPZ10         | 790mm  | 1000mm | 24mm  | 1000mm               | 790 x 899mm  | Mild Steel, Stainless Steel |
| GCPZ12         | 790mm  | 1200mm | 24mm  | 1200mm               | 790 x 1099mm | Mild Steel, Stainless Steel |
| GCPZ06         | 790mm  | 600mm  | 24mm  | 600mm                | 790 x 499mm  | Mild Steel, Stainless Steel |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**