

Muovinen läpivientiholkki | Seinäkotelot, CPG



The compression of each cable fitted in this cable gland can be adjusted, and is secured using a locking nut, which provides strain relief as well as a high ingress protection.

FEATURES

Description: Traditional cable fittings. Known for excellent strain relief even while providing a high protection class. Plastic lock nuts for fixation are included in the delivery.

Material: Fitting body made of polyamide PA6, and sealing made of neoprene.

Temperature resistance: -20°C to +100°C.

Flammability: V-2 according to UL94.

Finish: RAL 7035.

Protection: IP 66

Color: Light Gray
Material: Polyamide 6; Neoprene
Color Code: RAL 7035
Finish: Smooth

SPECIFICATIONS

Catalog Number	Height	Width	Depth	Enclosure Material	Product Family	Thread Size
CPG12	31mm	15mm	17mm	Mild Steel	Wall Mounted	M12 x 1.5
CPG16	40mm	22mm	24mm	Mild Steel	Wall Mounted	M16 x 1.5
CPG20	40mm	24mm	26mm	Mild Steel	Wall Mounted	M20 x 1.5
CPG25	46mm	33mm	35mm	Mild Steel	Wall Mounted	M25 x 1.5

Catalog Number	Height	Width	Depth	Enclosure Material	Product Family	Thread Size
CPG32	56mm	42mm	44mm	Mild Steel	Wall Mounted	M32 x 1.5
CPG40	68mm	53mm	55mm	Mild Steel	Wall Mounted	M40 x 1.5
CPG50	71mm	60mm	62mm	Mild Steel	Wall Mounted	M50 x 1.5
CPG63	71mm	65mm	67mm	Mild Steel	Wall Mounted	M63 x 1.5

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE