

19" leveydensäätimet, CIWR



These profiles are fixed to the enclosure's frame within 800 mm wide enclosures, at partial or full height, for mounting 19" profiles. They can also be used to reinforce full height 19" profiles by mounting them across the centre of the enclosure.

FEATURES

Description: Used to obtain 19" mounting facilities in 800 mm wide enclosures. Allows the mounting of CIP/CIPP profiles on partial or full height at any depth.

Material: 1.5 mm zinc plated steel.

Maximum load: Maximum supported weight is 5000N on 2 pair of CIWR and 8000N on 3 pair of CIWR.

Pack quantity: 1 pair with mounting accessories.

Thickness: 2mm
Material: Mild Steel
Finish: Zinc Plated

SPECIFICATIONS

Catalog Number	Height	Width	Depth	Mounting Plate Width	Enclosure Material
CIWR8196	80mm	800mm	600mm	19mm	Mild Steel
CIWR8198	80mm	800mm	800mm	19mm	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.