

Ylä- ja alapaneelit tuuletusaukoin | Lattiakaapit, DPCV

Both the enclosure's aesthetics and IP-rating are maintained when a complete set of doors and panels are mounted. The ventilation panels also provide natural ventilation.



FEATURES

Description: Required to cover the remaining space at the top and bottom. With ventilation slots for added heat dissipation in switchgear enclosures. Used in combination with horizontal dividers CDH/CDHK

Material: 1.75 mm steel plate.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 20.

Mounting requirements: DPCV covers 200 mm in height of the enclosure. So for a 2000 mm high enclosure when DPCV is used, there is 1800 mm space left for partial doors/panels.

Pack quantity: 2 panels with mounting accessories.

Thickness:	1.75mm
Color:	Light Gray
Material:	Mild Steel
Finish:	Powder Coated
Color Code:	RAL 7035

SPECIFICATIONS

Catalog Number	Height	Width	Depth	Height 1	Height 2	Product Family
DPCV0716R5	104mm	600mm	17mm	70mm	100mm	Free-Standing

Catalog Number	Height	Width	Depth	Height 1	Height 2	Product Family
DPCV0714R5	104mm	400mm	17mm	70mm	100mm	Free-Standing
DPCV0718R5	104mm	800mm	17mm	70mm	100mm	Free-Standing

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE