

nVent LENTON Interlok HY15LM Grout



The nVent LENTON Interlok HY15LM grout is a proprietary, nonmetallic, high-strength, nonshrink grout developed exclusively for the nVent LENTON Interlok coupling system. The nVent LENTON Interlok HY15LM grout is produced under strict nVent quality guidelines in order to ensure product quality along with consistent and reliable performance.

FONCTIONS

Cures quickly, allowing early removal of bracing systems

Nonmetallic grout will not rust or stain structures

Designed to provide superior dynamic, seismic and ultimate strength performance for moment frame applications

For use in pump or gravity fill applications



SPÉCIFICATIONS

Référence catalogue	Résistance à la compression	Température de fonctionnement	Poids unitaire	Quantité par colis
HY15LM	24.1 MPa @ 1 d, 110.3 MPa @ 28 d	0 to 38 °C	22.68 kg	1

Conçu pour respecter les normes suivantes :

ACI 318 type 1-ASTM A615 grade 60;ACI 318 type 1-ASTM A615 grade 75;ACI 318 type 1-ASTM A615 grade 80;ACI 318 type 1-ASTM A706 grade 60;ACI 318 type 1-ASTM A706 grade 80;ACI 318 type 2-ASTM A615 grade 60;ACI 318 type 2-ASTM A615 grade 75

INFORMATIONS COMPLÉMENTAIRES

Compressive Strength is based on room temperature tests performed at 70°F (21°C).

The shelf life of nVent LENTON Interlok Grout is 12 months from the manufacturing date printed on the bag.

nVent LENTON Interlok Grout should be stored in a cool, dry environment. It is recommended that the nVent LENTON Interlok Grout be stored indoors to maintain maximum shelf life and physical properties.

Prior to installation, please read and understand the detailed instructions and safety notices provided in the nVent LENTON Interlok Instruction Manual.

Part Number	Article Number	Rebar Size, Metric	Rebar Size, US	Rebar Size, Canada	Number of Couplers Per Bag of LENTON INTERLOK Grout
LK5	145575	16 mm	#5	15M	24
LK6	145580	20 mm	#6	20M	25
LK7	145585	22 mm	#7	-	26
LK8	145590	25 mm	#8	25M	21
LK9	145595	28 mm	#9	30M	17
LK10	145600	32 mm	#10	-	13.5
LK11	145605	36 mm	#11	35M	11.5
LK40	145610	40 mm	-	-	7
LKT14	145611	43 mm	#14	45M	7
LKT50	145615	50 mm	-	-	4
LKT18	145620	57 mm	#18	55M	4.5

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur www.nvent.com et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.

Amérique du Nord

+1 800 753 9221
Option 1 – Service client
Option 2 – Assistance
technique

Europe

Pays-Bas :
+31 800-0200135
France :
+33 800 901 793

Europe

Allemagne :
800 1890272
Autres pays :
+31 13 5835404

APAC

Shanghai :
+ 86 21 2412 1618/19
Sydney :
+61 2 9751 8500



Notre portefeuille puissant de marques:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE