

Unità ventola da 19", 1 U, controllo remoto e monitoraggio, 6 ventole, 100-240 VCA

CODICE A CATALOGO

10713-554

Unità ventola con interfaccia Modbus per l'installazione in uno spazio di 1 U all'interno dell'armadietto

CARATTERISTICHE

Controllo della temperatura della velocità della ventola

Interfaccia Modbus per monitoraggio e controllo remoti

Soglia di temperatura per il comando della ventola regolabile sul pannello anteriore

Segnalazione di guasto della ventola e sovratemperatura tramite 2 LED e uscite relè prive di potenziale

Alimentatore integrato con ampia gamma d'ingresso (100 V ? 240 V)

Meno di 1 U (42 mm) per consentire il montaggio su guide scorrevoli o cassette

2 sensori di temperatura NTC con cavi inclusi



ATTRIBUTI DEL PRODOTTO

Tipo di prodotto: Unità ventola

Tensione di ingresso CA: 100 – 240V

Flusso d'aria: 1089m³/h

Livello di rumorosità: 59.5dB(A)

Potenza: 97W

Pressione statica massima: 78Pa

Temperatura ambiente: -10 to 70°C

Durata, L10 a 40 C: 99558h

Quantità nella confezione: 1

Finitura: Alluminio zincato; Anodizzato

Peso lordo: 5.2kg

Materiale: Acciaio; Alluminio

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Il nostro straordinario portafoglio di marchi:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE