

Unità di controllo per LHX+ 5 kW e 10 kW

CODICE A CATALOGO

23130-668



L'unità di controllo arricchisce l'LHX+. Si collega ai sensori LHX+ e alla valvola motorizzata del liquido di raffreddamento 23130-607. Ciò consente al refrigeratore di controllare il flusso dell'aria del liquido di raffreddamento in base a un punto di regolazione della temperatura dell'aria raffreddata (alimentazione). Fornisce funzionalità avanzate di monitoraggio remoto e varie funzioni di configurazione.

CARATTERISTICHE

Controllo del flusso del liquido di raffreddamento basato sul punto di regolazione della temperatura dell'aria raffreddata (alimentazione). Più funzioni di controllo con il pacchetto per il controllo dell'acqua

Unità di controllo compatta da 19" separata senza fili allentati nella sezione superiore dell'armadio

Collegamenti del sensore plug & play chiaramente contrassegnati

ATTRIBUTI DEL PRODOTTO

Altezza: 88mm

Profondità: 220mm

Funziona con: Varistar; Varistar CP

Quantità nella confezione: 1

Colore: Grigio nero

Codice colore: RAL 7021

Finitura: Alluminio zincato

Tensione di ingresso CA: 230V

Materiale: Acciaio

Famiglia di prodotti: Varistar CP

Tipo di prodotto: Unità di controllo

Altezza del rack: 2U

Larghezza: 439.5mm

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

INFORMAZIONI DI PRODOTTO AGGIUNTIVE

Display esterno opzionale.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Il nostro straordinario portafoglio di marchi:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE