

Guida orizzontale, anteriore, tipo R-KD, robusta, labbro corto, 84 CV



Combinations of horizontal rails and side panels

	Light = L	Plastic = F	Heavy = H	Support = R
Standard rail	-	+	+	+
Standard rail with side panel	+	+	+	+
Standard rail with side panel (for connection)	+	+	+	+
Standard rail with side panel (for connection) (not recommended)	+	+	-	-
Standard rail with side panel (for connection) (not recommended) (not recommended)	+	+	-	-

Light = L, Plastic = F, Heavy = H, Support = R

CODICE A CATALOGO

34566-284

La robusta guida orizzontale è in grado di gestire urti e vibrazioni fino a 25 g..

CARATTERISTICHE

Guida orizzontale "robusta" di tipo R-KD con fissaggio a 3 fori per una maggiore robustezza

Alluminio estruso, finitura anodizzata, superficie di contatto conduttiva, con contrassegni HP



ATTRIBUTI DEL PRODOTTO

Larghezza rack: 84HP

Quantità nella confezione: 1

Finitura: Anodizzato

Lunghezza: 431.8mm

Materiale: Alluminio

Famiglia di prodotti: EuropacPRO

Tipo di prodotto: Guida orizzontale

Tipo: Robusto, KD

Funziona con: Rack secondari

Peso lordo: 0.26kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

INFORMAZIONI DI PRODOTTO AGGIUNTIVE

Senza filettatura M4 sul lato anteriore, senza stampa e senza tacca per staffa da 19".

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Il nostro straordinario portafoglio di marchi:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE