

Backplane di alimentazione CPCI con connettore P 47, 6 U, 8 CV, 2x P47

CODICE A CATALOGO

23098-396

Backplane di alimentazione per applicazioni CompactPCI.
Con connettore di alimentazione P47.

CARATTERISTICHE

In conformità a: Specifiche dell'interfaccia di
alimentazione CompactPCI PICMG 2,11 R1.0

In conformità a: Specifiche del bus di gestione del sistema
PICMG 2,9 R1.0

Possibilità di funzionamento singolo, parallelo o
ridondante

Indirizzo geografico regolabile

Alimentazione tramite contatti a crimpare inseriti nella
spina, nessuna tensione di alimentazione sul backplane

Cavo di alimentazione disponibile come accessorio

Uscite c.c. con Power bugs per cadute di tensione
estremamente basse



ATTRIBUTI DEL PRODOTTO

Tipo di prodotto: Backplane

Numero di scanalature: 1

Altezza del rack: 6U

Tipo di backplane: Backplane di alimentazione CompactPCI con P47

Larghezza asola: 8HP

Tipo di connettore di alimentazione: (2) P47

Tipo di connettore di servizio: SMCQ, 12 pin; MicroMatch, 10 pin

Larghezza: 39.6mm

Peso lordo: 0.391kg

Quantità nella confezione: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Il nostro straordinario portafoglio di marchi:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE