

# Kit di schermatura EMC EuropacPRO, piastra di copertura su guida orizzontale, acciaio inox, 42 CV, 10 pezzi

## CODICE A CATALOGO


**24560-241**

La guarnizione in acciaio inox è agganciata in una scanalatura della guida orizzontale e consente il contatto con la piastra di copertura.

## CARATTERISTICHE

La guarnizione in acciaio inox è agganciata alla guida orizzontale e forma la piastra di copertura a contatto

Si adatta a tutte le guide orizzontali



## ATTRIBUTI DEL PRODOTTO

Larghezza rack: 42HP

Quantità nella confezione: 10

Materiale: Acciaio inossidabile

Famiglia di prodotti: EuropacPRO

Tipo di prodotto: Kit di schermatura

Funziona con: Rack secondari

Peso lordo: 0.037kg

\*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

## INFORMAZIONI DI PRODOTTO AGGIUNTIVE

Quando si utilizza un cofano posteriore, la guarnizione EMC in acciaio inossidabile garantisce il collegamento conduttivo tra la guida orizzontale e il cofano posteriore.

## AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su [www.nvent.com](http://www.nvent.com) e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Il nostro straordinario portafoglio di marchi:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**