


Plug-in unit-kit met IEL-handgreep voor I/O achter, afgeschermd, zwart, 3 u, 8 pk



CATALOGUSNUMMER

20848-752

Plug-in-eenheid, met zwarte handgreep voor IEL-insteekmachine/uitneemgereedschap, 3 u, I/O-eenheid achter. Het u-vormige voorpaneel maakt afscherming mogelijk met een textielpakking.

KENMERKEN

U-vormig voorpaneel voor textielpakking

Geschikt voor insteek- en extractiekrachten tot 700 N (per paar)

Schakel de installatie van een microschakelaar in

De installatie van codeerpennen in overeenstemming met IEC 60297-3-103/ IEEE 1101,10 mogelijk maken



PRODUCTKENMERKEN

Rekbreedte: 8HP

Hoeveelheid in verpakking: 1

Type handgreep: IEL

Montage: Opschroefbare IO aan achterzijde

Type pakking: Textiel

Afwerking voorzijde: Geanodiseerd

Afwerking achterzijde: Geëtst

Behandelde randen: Nee

Voldoet aan: IEC 60297-3-102; IEEE 1101,10; IEC 60297-3-103; IEEE 1101,1/11

EMC-afscherming: Ja

Afwerking: Geanodiseerd; Geëloxeerd

Hoogte (H): 128.4mm

Materiaal: Aluminium

Producttype: Frontpaneel

Rekhoogte: 3U

Type: Frontpaneel met handgreep (PIU)


Breedte (W): 40.3mm

Nettogewicht: 0.1kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DIAGRAMMEN

3U



WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE