

PXI Express-controller, 4 pk, I5-1145G7E 32-1024

CATALOGUSNUMMER

21265-124



De geïntegreerde nVent SCHROFF PXIe-controller is de meest compacte en krachtige 3U-controller met één sleuf voor de PXI Express- en CPCIexp-platforms. Met zijn enorme en toekomstbestendige interfacemogelijkheden werkt hij perfect met de meeste test- en meettoepassingen. De Controller wordt aangedreven door een 11e generatie Intel® Core™ i3 / i5 processors in combinatie met maximaal 64 GB DDR4 geheugen en ondersteunt eenvoudig toepassingen met hoge bandbreedte met toekomstige PCIe Gen4 en dubbele 2500BASE-T systeem interconnectiviteit.

KENMERKEN

PXI Express-systeemcontroller, 3 u, 4 HP, met Intel Core I5-1145G7E-processor

PXI-5 PXI Express hardwarespecificaties. Voldoet aan Rev.2,0

PCIe-bandbreedte van maximaal 14 GB/s

Upgradebare m.2 NVMe- en DDR4-opslag

3x USB3.1, 2x GbE en 1x DP 1,2 op het voorpaneel

Volledig aanpasbare AMI Aptio® Embedded BIOS

PRODUCTKENMERKEN

Producttype: Systeem

Type: Regeleenheid

Gegevensoverdracht: PCIe Gen3

Rekhoogte: 3U

Voldoet aan: PXISA PXI-5 R1.1

Diepte: 160mm

Nettogewicht: 0.4kg

Hoeveelheid in verpakking: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

AANVULLENDE PRODUCTGEGEVENS

Conform PICMG rev. 3,0 en PXI-6.

Aangepaste controllers beschikbaar op aanvraag.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE