

Controller voor LHX+ 5 kW en 10 kW

CATALOGUSNUMMER

23130-668



De regeleenheid verrijkt de LHX+. Deze wordt aangesloten op de LHX+-sensoren en de gemotoriseerde koelvloeistofklep 23130-607. Hierdoor kan de koeler de koelvloeistofstroom regelen op basis van een instelwaarde voor de temperatuur van de gekoelde (toevoer)lucht. Het biedt geavanceerde functionaliteit voor bewaking op afstand en diverse instellingsfuncties.

KENMERKEN

Regeling van de koelvloeistofstroom op basis van de instelwaarde voor de temperatuur van de gekoelde lucht (toevoer). Meer bedieningsfuncties met waterregelingspakket

Aparte, compacte 19" Regeleenheid zonder losse draden in het bovenste deel van de kast

Duidelijk gemarkeerde plug & play-sensoraansluitingen

PRODUCTKENMERKEN

Hoogte: 88mm

Diepte: 220mm

Werkt met: Varistar; Varistar CP

Hoeveelheid in verpakking: 1

Kleur: Zwartgrijs

Kleurcode: RAL 7021

Afwerking: Aluminium-verzinkt

Ingangsspanning AC: 230V

Materiaal: Staal

Productserie: Varistar CP

Producttype: Regeleenheid

Rekhoogte: 2U

Breedte: 439.5mm

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail

price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

AANVULLENDE PRODUCTGEGEVENS

Optioneel extern beeldscherm.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE