

Horizontale rail, voor, Type R-KD, robuust, korte lip, 40 pk



Combinations of horizontal rails and side panels

	"B" can be combined		"C" combinations not recommended	
Upper 1/3		-		not recommended
Upper 2/3		not recommended		not recommended
Upper 1/3 + Upper 2/3		+		+
Horizontal rail		+		-
Side panel		+		+
Upper 1/3 + Horizontal rail		+		+
Upper 2/3 + Horizontal rail		+		+
Upper 1/3 + Upper 2/3 + Horizontal rail		+		+
Upper 1/3 + Side panel		+		+
Upper 2/3 + Side panel		+		+
Upper 1/3 + Upper 2/3 + Side panel		+		+

CATALOGUSNUMMER

34566-240

De robuuste horizontale rail is bestand tegen schokken en trillingen tot 25 g.

KENMERKEN

Type R-KD „robuuste” horizontale rail met bevestiging met 3 gaten voor extra robuustheid

Aluminium extrusie, geanodiseerde afwerking, geleidend
contactoppervlak, met HP markeringen



PRODUCTKENMERKEN

Rekbreedte: 40HP

Hoeveelheid in verpakking: 1

Afwerking: Geanodiseerd

Length: 208.28mm

Materiaal: Aluminium

Productserie: EuropacPRO

Producttype: Horizontale rail

Type: Robuust, KD

Werkt met: Subracks

Brutogewicht: 0.118kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

AANVULLENDE PRODUCTGEGEVENS

Zonder M4-schroefdraad naar voren, zonder afdrukken en zonder inkeping voor 19-inch beugel.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE