

19-inch ventilatoreenheid, 1 u, afstandsbediening en bewaking, 6 ventilatoren, 100-240 VAC



CATALOGUSNUMMER

10713-554

Ventilatoreenheid met Modbus-interface voor installatie in een ruimte van 1 u in de kast

KENMERKEN

Temperatuurregeling ventilatortoerental

Modbus-interface voor bewaking en besturing op afstand

Temperatuurdrempel voor de ventilatorregeling instelbaar op het voorpaneel

Signalering van ventilatorstoring en oververhitting door 2 LED's en potentiaalvrije relaisuitgangen

Geïntegreerde voeding met breed ingangsbereik (100 V ? 240 V)

Minder dan 1 u (42 mm) voor montage op schuifrails of lade

2 NTC-temperatuursensoren inclusief kabels



PRODUCTKENMERKEN

Producttype: Ventilatoreenheid

Ingangsspanning AC: 100 – 240V

Luchtstroom: 1089m³/h

Geluidsniveau: 59.5dB(A)

Voeding: 97W

Max. statische druk: 78Pa

Omgevingstemperatuur: -10 to 70°C

Levensduur, L10 bij 40 C: 99558h

Hoeveelheid in verpakking: 1

Afwerking: Aluminium-verzinkt; Geanodiseerd

Brutogewicht: 5.2kg

Materiaal: Staal; Aluminium

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE