

Regeleenheid ventilatortoerental (kit)

CATALOGUSNUMMER

20118-900

Geschikt voor alle AC-ventilatoren en ventilatoren (tot 300 W) met IEC 60320 C13- en C14-stekker (plug & play).

Bestel de huidige ingangsdraad/netkabel afzonderlijk

KENMERKEN

De externe sensor kan op een gewenst meetpunt worden ingesteld

Open-collector uitgang (parametriseerbaar) ? Alarmuitgang (actief/passief) ? DC-ventilatoren (PWM-uitgang) ? Display op afstand (via optioneel digitaal display met voorpaneel)

Wordt gemonteerd op de meegeleverde steunrail

Geschikt voor alle AC-, EC- en EC-ventilatoren en ventilatoreenheden (tot 300 W) met IEC 60320, connectoren IEC C14 en C13

Eenvoudige instelling van inschakeltemperatuur (met knop en digitaal display)

Stroomingangsdraad/netkabel kan worden gekozen op basis van de projectvereisten: SCHUKO-UTE / IEC / BS



PRODUCTKENMERKEN

Producttype: Ventilatorregelmodule

Werkt met: Varistar CP

Materiaal: Kunststof

Nettogewicht: 0.588kg

Hoeveelheid in verpakking: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent

klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE