


Plug-in Unit Kit voor PMC met IEL-handgreep zwart, u-vormig voorpaneel afgeschermd (textiel), 3 u, 4 HP



CATALOGUSNUMMER

20836-460

U-vormig voorpaneel met uitsparing voor PMC.
Afgeschermd voor EMC-pakking van textiel.

KENMERKEN

In overeenstemming met IEEE P1386, PCI-mezzaninekaart

Voor enkele modules van 69,0 x 76,5 mm of dubbele
modules van 139,0 x 76,5 mm

Voor standaard gedefinieerde I/O mezzanie-modules die
worden aangesloten op draagkaarten

PMC = PCI-mezzaninekaart

FPGA = Field Programmable Gate Array

Voorpaneel met u-profiel 3 u, 4 pk, met textielpakking

EMC-afscherming voor voorpaneel en bekleding voor
uitsparingen in voorpaneel

PRODUCTKENMERKEN

Rekhoogte: 3U

Hoeveelheid in verpakking: 1

Type handgreep: IEL

Montage: Opschroefbare voorzijde

Type pakking: Textiel

Afwerking voorzijde: Geanodiseerd

Afwerking achterzijde: Geleidend

Voldoet aan: PMC Mezzanine, IEEE P1386

EMC-afscherming: Ja

Afwerking: Geanodiseerd; Geëloxeerd

Materiaal: Aluminium

Producttype: Frontpaneel

Rekbreedte: 4HP

Type: Frontpaneel met handgreep (PIU)

Nettogewicht: 0.088kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE