

LHX+-kit voor waterregeling

CATALOGUSNUMMER

23130-663



De roestvrijstalen pijpinzetstukken met een binnendiameter van 1 inch worden elk geleverd met een paar ratiometrische koelvloeistofsensoren. De sensoren worden rechtstreeks aangesloten op de controller van het achterportier van de rackchiller. Dit maakt bewaking van de thermische eigenschappen en koeling van de koelvloeistof mogelijk, evenals extra functies voor temperatuurregeling.

KENMERKEN

Retoursensoren: Stroming en temperatuur van de koelvloeistof

Stelt de regelaar in staat de flow te moduleren op basis van de retourtemperatuur

Waterregeleenheid met waterstroming, temperatuursensor

Beide pijpinzetstukken van roestvrij staal die met bouten aan de bodemplaat kunnen worden bevestigd om een hoge EMC- en IP-waarde te garanderen

PRODUCTKENMERKEN

Producttype: Connectorset

Werkt met: Varistar; Varistar CP

Brutogewicht: 0.576kg

Hoeveelheid in verpakking: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

AANVULLENDE PRODUCTGEGEVENS

LHX+-controller vereist.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE