

CPCI-systeem met ATX-voeding. Desktop, 4 u, 8 sleuven, 84 HP

CATALOGUSNUMMER

24579-602

CompactPCI-desktopchassis met verticale kaartbehuizing voor acht 3 u-kaarten, acht 3 u RTM-kaarten en ingebouwde ATX-voeding.

KENMERKEN


In overeenstemming met IEC 60297-3-101, -102, -103; IEEE 1101.1, 1101.10/11; backplane in overeenstemming met PICMG 2,0 rev. 3,0

Systeem met verticale kaartbehuizing. Formaat bord voorzijde: 3 u, 160 mm diep; I/O achterzijde: 3 u, 80 mm diep

Backplane 8-sleuven, 3 u, 32 -bits, systeem sleuf rechts; 8 HP Wide CPU's kunnen worden gebruikt

Warmteafvoer door twee radiale ventilatoren, luchtstroom voor naar achter

ATX-VOEDING, 300 W



PRODUCTKENMERKEN

Producttype: Systeem

Aantal sleuven: 8

Type: Desktop

Type achterzijde: 3 U CompactPCI

Gegevensoverdracht: 32-bits PCI-bus

Vermogen per sleuf: 40W

Ingangsspanning AC: 100 – 240V

Luchtstroomrichting: Voor naar achter

Rekhoogte: 4U



Type voeding: (1) ATX-VOEDING

Voeding inbegrepen: Ja

I/O achter: Ja

Voldoet aan: PICMG 2,0 R3.0

Diepte: 275mm

Hoogte: 177mm

Nettogewicht: 10.7kg

Hoeveelheid in verpakking: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

AANVULLENDE PRODUCTGEGEVENS

Aangepaste systemen beschikbaar op aanvraag.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE