

Varmeovner for farlig plassering



Designed for hazardous locations where electronic components require protection from cold freezing temperatures, condensation and corrosion.

BRANSJESTANDARDER

ATEX, IECEx

II2G Ex d IIC T3 / II2 D Ex Td A21 IP65 T200 C

NEC CSA us

Class I, Div 1 Groups A, B, C, D / Class II Div 1 Groups E, F, G

FUNKSJONER

50W, 80W, 200W, 300W, 400W and 600W models available

Provides freeze protection down to -76 F / -60 C

Conductive and Convection heating types available

50W and 80W models can be mounted directly to manifolds, measuring or analyzing instruments, control valves, and similar equipment

200W, 300W, 400W, 600W models are finned heaters that heat the area by transferring the heat from the heater to surrounding air, creating a convection current

Two thermostat options available with a 50 F / 10 C or 68 F / 20 C set point

Materiale: Aluminium

Overflate: Anodisert

Farge: Svart

SPESIFIKASJONER

Katalognummer	Høyde	Bredde	Dybde	Nominell spenning	Oppvarmingskapasitet	Spennings AC
HLTSTAT10C	28mm	23mm	109mm			
HLTSTAT20C	28mm	23mm	109mm			
DAHHL501AC	89mm	41mm	30mm	115V	50W	110V
DAHHL801AC	89mm	41mm	30mm	115V	80W	110V

Katalognummer	Høyde	Bredde	Dybde	Nominell spenning	Oppvarmingskapasitet	Spenning AC
DAHHL4001A	226mm	229mm	61mm	115V	400W	110V
DAHHL6001A	325mm	229mm	61mm	115V	600W	110V
DAHHL6002A	325mm	229mm	61mm	220V	600W	207V
DAHHL4002A	226mm	229mm	61mm	220V	400W	207V
DAHHL300AC	325mm	229mm	61mm	115V	300W	110V
DAHHL200AC	226mm	229mm	61mm	115V	200W	110V

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE