

PSU 19-tommers AC/DC for MicroTCA, med administrasjon (PM EMMC) dobbel full størrelse

KATALOGNUMMER

11098-547



MTCA PSU 600 er en eksepsjonelt effektiv strømodul (PM) for MicroTCA-applikasjoner. Denne 600W strømforsyningen er den mest effektive tilgjengelige i dobbel bredde full størrelse format. Denne PM integrerte styringskontrolleren gjør den ideell for bruk i komplekse kommunikasjonssystemer som kjører de nyeste generasjonene av prosessorer og et økt antall AMC-moduler. MTCA PSU 600 gir strøm som kreves for 12 AMC-er, 2 kjøleenheter (CU) og 2 MicroTCA Carrier Hubs (MCHS).

FUNKSJONER

Dobbel høyde full størrelse bredde



PRODUKTEGENSKAPER

Produkttype: Strømforsyning

Type: 19-tommers vekslemodus

Fungerer med: MicroTCA-systemer

Inngangsspenning AC: 90 – 264V

Effekt: 600W

Antall utgangsspenninger: 2

Spenning 1: 12V

Strøm 1: 6.8A

Spenning 2: 3.3V

Strøm 2: 0.18A

Rackbredde: 6HP

Dybde: 186.65mm

Høyde: 148.3mm

Nettovekt: 1.315kg

Antall pakker: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YTTERLIGERE PRODUKTDETALJER

Utgangsdata for ta = ? 25 ... 55 °C med tvungen kjøling på 20 cfm.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmaterieil. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vår solide portefølje av merkevarer:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE