

VPX-system, robust, 10 U, 10-spor, Pluggable PSU

KATALOGNUMMER

20836-780

Robust VPX-system for 10 VPX-kort 6 U, 1 tommer, 160 mm og 10 i/O-brett bak. Strømmen til systemet leveres av en pluggbar VPX strømforsyning. En viftestyremodul overvåker viftene, temperaturen og spenningen.

FUNKSJONER

System konstruert i henhold til: MIL-STD-810F, MIL-STD-167, MIL-STD-461, IP 20

For robuste applikasjoner med økt støt- og vibrasjonsmotstand

PSU, 1 pluggbar strømforsyning, 1000 W, 6 U, plass til en andre PSU

Bakplan VPX 10 spor, 6 U, i henhold TIL Vita 65, bakplan profil BKP6-CEN10-11.2.4.4

100 til 240 VAC-inngang bak, hovedbryter foran på chassiset

LED-indikator for spenning og viftefeil foran

6 U fremre kortbur og 6U bakre i/O-kortbur, med 10 Slot VPX bakplan

Klar for teleskopiske lysbilder

Optimal EMC-beskyttelse gjennom hengslet front- og bakpanel med integrert Honeycomp-filter



PRODUKTEGENSKAPER

Produkttype: System

Antall spor: 10

Type: Robust 19-tommers rackfeste

Bakplantype: VVPX, VITA 65

Dataoverføring: 10 GbE; PCIe Gen3

Strøm per spor: 50W

Inngangsspenning AC: 100 – 240V

Luftstrømretning: Front til bakside

Rackhøyde: 10U

Strømforsyningstype: (1) Pluggbar PSU

Strømforsyning inkludert: Ja

Bakre i/U: Ja

Samsvarer med: ANSI/VITA 46.0-2019

Effekt: 1000W

Dybde: 490mm

Høyde: 443.7mm

Bredde: 480mm

Nettvekt: 32kg

Antall pakker: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YTTERLIGERE PRODUKTDETALJER

Modifiserte systemer tilgjengelig på forespørsel.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmaterieill. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vår solide portefølje av merkevarer:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE