

VME64x-system, 8 U, 21-spor, åpen rammePSU

KATALOGNUMMER

20836-820

VME64-system for 21 VME64x-plater 6 U, 160 mm. bakre i/O-alternativ strømmen leveres av en strømforsyning med åpen ramme. En viftestyremodul overvåker viftene, temperaturen og spenningen.

FUNKSJONER

System i samsvar med IEC 60297-3-101, 102, 103; IEEE 1101,1 , 1101,10/11; bakplan samsvarer med VITA 1,1-1997


PSU, åpen ramme, 642 W (600 W ved < 180 VAC)

Bakplan VME64x 21 -spor, 6 U, J1/J2 monolittisk med P0-kontakt, i samsvar MED VITA 1-1994 og 1.1-1997

Varmespredning av 3 vifter, kjøling fra bunn til topp; temperaturkontrollert av viftestyremodul (FCM)

System for standard bordmontering med brettformat, 6 U, 160 mm dyp, bakre i / O alternativ

Skjermmodul for DC-driftsspenninger, vifte og temperaturalarm



PRODUKTEGENSKAPER

Produkttype: System

Antall spor: 21

Type: 19-tommers rackfeste

Bakplantype: 6 U VME64-forlengelse

Dataoverføring: VME64; VME2eSST

Strøm per spor: 30W

Inngangsspenning AC: 100 – 240V

Luftstrømretning: Bunn til topp

Rackhøyde: 8U

Strømforsyningstype: Åpen ramme

Strømforsyning inkludert: Ja

Bakre i/U: Ja

Samsvarer med: ANSI/VITA 1.1-1997

Dybde: 412mm

Høyde: 354.8mm

Bredde: 449mm

Effekt: 600W

Nettvekt: 19kg

Antall pakker: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YTTERLIGERE PRODUKTDETALJER

Modifiserte systemer tilgjengelig på forespørsel.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vår solide portefølje av merkevarer:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE