

PXI Express Controller, 4 HP, I5-1145G7E 32-1024

KATALOGNUMMER

21265-124



nVent SCHROFF innebygd kontrollert er den mest kompakte og kraftige 3U ett-spor innebygd kontrollert for PXI Express og CPClexp plattformer. Med sine enorme og fremtidsrettede grensesnitt evner, fungerer det perfekt med de fleste test- og måleapplikasjoner. Kontrollert drives av en 11. Generasjons Intel® Core™ i3-/i5-prosessorer kombinert med opptil 64 GB DDR4-minne, og støtter enkelt programmer med høy båndbredde med fremtidige klare PCIe Gen4 og dual 2500BASE-T-systemtilkobling.

FUNKSJONER

PXI Express System Controller, 3 U, 4 HP, med Intel Core i5-1145G7E prosessor

PXI-5 PXI Express maskinvare spec. Rev. 2.0-kompatibel

Maksimal PCIe-båndbredde på 14 GB/s

Oppgraderbar m.2 NVMe- og DDR4-lagring

3x USB3.1, 2x GbE og 1x DP 1,2 på frontpanelet

Fullstendig tilpassbar AMI Aptio® innebygd BIOS

PRODUKTEGENSKAPER

Produkttype: System

Type: Kontroller

Dataoverføring: PCIe Gen3

Rackhøyde: 3U

Samsvarer med: PXISA PXI-5 R1.1

Dybde: 160mm

Nettvekt: 0.4kg

Antall pakker: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YTTERLIGERE PRODUKTDETALJER

I samsvar med picmg rev. 3,0 og PXL-6.

Modifiserte kontrollere tilgjengelig på forespørsel.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE