

Rack Safety Plus, 3 U, 230 V AC, C20, C13/Schuko

KATALOGNUMMER

21270-011

nVent SCHROFF Rack Safety Plus-enheten er en 19-tommers strømfordelingsenhet som brukes til å levere nettstrøm til elektriske eller elektroniske enheter som en sentral strømbryter. I tillegg er den utstyrt med en nødstoppfunksjon.

FUNKSJONER

19", 3 U strømfordelingsenhet med nødstoppfunksjon

Leverer nettstrøm til elektriske eller elektroniske enheter som en sentral strømbryter

400 V 3-faset eller 230 V 1-faset nettinngang med nettsikringer

AC-utganger med forskjellige kontakttypen, slått av AV/PÅ-bryter

Permanente vekselstrømutganger (service)

Alle utganger er beskyttet av effektbrytere

Nødstoppfunksjonen oppfyller kravene i NS-en 60947-5-1 og NS-en 60204-1 og er vandalismesikker

En ekstra ekstern nødstoppknapp kan kobles til systemet



PRODUKTEGENSKAPER

Produkttype: Strømfordeler

Fungerer med: Varistar CP; Novastar

Funksjon: Nødstop

Inngangsspenning AC: 230V

Antall faser: 1

EMC-filter: Nei

Overspenningsavleder: Nei

Begrensning for innkoblingsstrøm: Nei

Reststrømninnetning: Ja

Deksel for kretsbytter: Nei

Rackhøyde: 3U

Kontakttype: SCHUKO; IEC C13

Tilbehørstype: Strømfordelingstilbehør

Nettvekt: 12kg

Antall pakker: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YTTERLIGERE PRODUKTDETALJER

For nøyaktig konfigurasjon av valgfrie funksjoner og eksempelkonfigurasjon, se tabellen(e) som leveres.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmaterieil. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vår solide portefølje av merkevarer:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE