

Styreenhet for LHX+ 5 KW og 10 KW

KATALOGNUMMER

23130-668



Kontrollenheten beriker LHX+. Den kobles til LHX+-sensorene og den motoriserte kjølevæskeventilen 23130-607. Dette gjør det mulig for kjøleren å kontrollere kjølevæskeluftstrømmen basert på et innstillingspunkt for kjølt (tilluftsluft). Det gir avansert ekstern overvåking funksjonalitet og ulike oppsett funksjoner.

FUNKSJONER

Regulering av kjølevæskestrømmen basert på innstillingspunktet for kjølevæsketemperatur (tilluftsluft). Flere kontrollfunksjoner med vannkontrollpakke

Separat, kompakt 19" Styreenhet uten løse ledninger i overskap

Tydelig merkede plug & play-sensortilkoblinger

PRODUKTEGENSKAPER

Høyde: 88mm

Dybde: 220mm

Fungerer med: Varistar; Varistar CP

Antall pakker: 1

Farge: Svart grå

Fargekode: RAL 7021

Overflate: Belagt med aluminiumsink

Inngangsspenning AC: 230V

Materiale: Stål

Produktserie: Varistar CP

Produkttype: Kontrollenhet

Rackhøyde: 2U

Bredde: 439.5mm

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address,

parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YTTERLIGERE PRODUKTDETALJER

Valgfri ekstern skjerm.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vår solide portefølje av merkevarer:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE