

EuropacPRO dekselplate, Universal, 42 hk, 175 mm

KATALOGNUMMER

24560-031

En dekselplate brukes til elektromagnetisk skjerming eller som mekanisk beskyttelse. Dekselet kan brukes er ikke-standard boards vil bli montert i subrack.

FUNKSJONER

Skjerming leveres av EMC rustfrie stålpakninger, mellom dekselplate og sidepanel

For variabel posisjonering av horisontale skinner f.eks. for PCB med ikke-standardformater

Perforering grad 58%

Egnet for bruk med alle horisontale skinner



PRODUKTEGENSKAPER

Rackbredde: 42HP

Dybde: 175mm

Antall pakker: 2

Overflate: Passivert

Materiale: Aluminium

Produktserie: EuropacPRO

Produkttype: Dekkplate

Type: Universell

Fungerer med: Delrack

Nettovekt: 0.21kg

Pakkeenhet: Par

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address,

parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YTTERLIGERE PRODUKTDETALJER

I tillegg er det nødvendig med 4 kontaktstrimler per slick for å feste dekselet på horisontal skinne.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE