

EuropacPRO bakre hette for EMC-pakning i rustfritt stål, 3 U, 84 hk

KATALOGNUMMER

34561-752

Den bakre hetten brukes som en skjermet bakre grense og krever 60 mm plass. Hvis bakhetten derfor brukes, må sidepaneldybden være 60 mm større enn tavledybden. Kontakt mellom bakhetten og de horisontale skinnene etableres av kontaktstrimmelen i rustfritt stål for dekselplaten. Det er derfor ikke behov for ytterligere EMC-tetning. Bakdeksel kan ikke brukes samtidig med hjørneprofilen bak.


FUNKSJONER

Den bakre hetten brukes som en skjermet bakre grense. Bakdekselet krever 60 mm plass. Hvis bakhetten derfor brukes, må sidepaneldybden være 60 mm større enn tavledybden. Eksempel: For en bretttybde på 160 mm brukes et sidepanel (med bakdeksel) på 235 mm (175 mm + 60 mm)

Kontakt mellom bakhetten og de horisontale skinnene etableres av kontaktstrimmelen i rustfritt stål for dekselplaten. Det er derfor ikke behov for ytterligere EMC-tetning

Bakdeksel kan ikke brukes samtidig med hjørneprofilen bak

For EMC-skjerming, bestill EMC-pakning for horisontal skinne separat.



PRODUKTEGENSKAPER

Rackhøyde: 3U

Rackbredde: 84HP

Antall pakker: 1

Overflate: Passivert

Materiale: Aluminium

Produktserie: EuropacPRO

Produkttype: Deksel

Type: Bakre panser

Fungerer med: Delrack

Bruttovekt: 0.339kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YTTERLIGERE PRODUKTDETALJER

Nødvendig antall skruer per bakdeksel: 3 U subrack 10 skruer; 6 U subrack 16 skruer.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmaterieil. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vår solide portefølje av merkevarer:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE