

Zasilacz 19" do CompactPCI, AC/DC, 3 U, 300 W

NUMER KATALOGOWY

13100-143

Zasilacz 19-calowy z P47 złączem, do zastosowań CompactPCI.

FUNKCJE

Złącze P47 i sygnalizacja CompactPCI

4 napięcia wyjściowe

Nadmiarowa praca z magistralą CSB (Current Share Bus), hot-swap



ATRYBUTY PRODUKTU

Typ produktu: Zasilanie

Typ: Tryb impulsowy 19"

Współpracuje z: Systemy CompactPCI; Systemy VME64x

Napięcie wejściowe AC: 90 – 264V

Zasilanie: 300W

Liczba napięć wyjściowych: 4

Napięcie 1: 5V

Prąd 1: 40A

Napięcie 2: 3.3V

Prąd 2: 40A

Napięcie 3: 12V

Prąd 3: 10A

Napięcie 4: -12V

Prąd 4: 2A

Wysokość stojaka: 3U

Szerokość stojaka: 8HP

Waga brutto: 1.014kg

Liczba opakowań: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on

SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Marki w naszej ofercie:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE