


**Uchwyt do wkładania/wyjmowania typu IEL,
czarna dźwignia, szary przycisk, Góra, 100
sztuk**

**NUMER KATALOGOWY**

20817-615

Uchwyt wkładki/ściągacza, typ IEL zgodnie z normą IEEE 1101.10. Dwa z tych uchwytów mogą pokonać siłę pojedynczej dźwigni 700N (na parę).

FUNKCJE

Nadaje się do sił wkładania i wyciągania do 700 N (na parę)

Zgodnie z normami IEEE 1101.10 i IEC 60297-3-102

Można zamontować mikroprzełącznik



ATRYBUTY PRODUKTU

Liczba opakowań: 100

Typ uchwytu: IEL; Górny przedni; Dolne tylne we/wy

Klasyfikacja palności: UL® 94V-0

Kolor: Czarny

Zgodność z: EN 45545-2

Materiał: Poliwęglan; Stop cynku

Typ produktu: Uchwyt

Typ: Przyrząd do wsuwania/wyciągania, standardowy

Współpracuje z: Panele przednie


Waga netto: 2.327kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DODATKOWE INFORMACJE O PRODUKCIE

Kołki kodowania i mikroprzełącznik należy zamówić oddzielnie.

SCHEMATY



OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
 +49.7082.794.0
 Betschdorf, France
 +33.3.88.90.64.90
 Warsaw, Poland
 +48.22.209.98.35
 Assago, Italy
 +39.02.932.7141
 Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Marki w naszej ofercie:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE